Food (Kitchen/Stainless Steel/IP65...68 Protection)

#### IP Protected Bench Scale KERN WTB









### Ideal for food industry, thanks to its IP65 protection and special checkweighing display, verification optional

#### **Features**

- · Ideal for the increased hygienic requirements in the food industries
- · Your support in a HACCP-compliant quality system
- 11 Protection against dust and water splashes IP65 (only when using rechargeable battery pack)
- Very fast display: steady weight values within 2 s
- 2 Second display on the back of the balance
- · Compact size, practical for small spaces
- $\blacksquare$  Innovative weighing with tolerance range (Checkweighing): The colour of the display changes depending on the weight (too light/ok/ too heavy) and is an aid to help with portioning, dosing and grading

- · High mobility: thanks to rechargeable battery operation (optional), compact, lightweight construction, it is suitable for the use in several locations
- · Recessed grips on the underside of the scale for easy transportation
- · Protective working cover included with delivery

#### Technical data

- · Large backlit LCD display, digit height 25 mm
- · Dimensions weighing surface, stainless steel,
- Overall dimensions W×D×H 286×316×126,5 mm
- · Net weight approx. 3,2 kg
- Permissible ambient temperature -10 °C/40 °C

#### Accessories

- · Protective working cover, scope of delivery 5 items, KERN RFB-A01S05
- · Internal rechargeable battery pack, operating time up to 50 h without backlight, charging time approx. 12 h, KERN WTB-A01N
- 4 Tare pan made from stainless steel, ideal for weighing loose small parts as well as fruits, vegetables, etc., overall dimensions W×D×H 400×300×45 mm, KERN RFS-A02

#### STANDARD

















Model	Weighing capacity	Readability	Verification value	Minimal load	Options	
					Verification	DAkkS Calibr. Certificate
	[Max]	[d]	[e]	[Min]	MIII	DAkkS
KERN	kg	g	g	g	KERN	KERN
WTB 1K-4N	1,5	0,2	-	-	-	963-127
WTB 3K-4N	3	0,5	-	-	-	963-127
WTB 6K-3N	6	1	-	-	-	963-128
WTB 10K-3N	15	2	-	-	-	963-128
WTB 30K-3N	30	5	_	-	_	963-128

Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order. The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.

WTB 3K-3NM	3	1	1	20	965-227	963-127	
WTB 1K-4NM	1,5	0,5	0,5	10	965-227	963-127	
WTB 6K-3NM	6	2	2	40	965-228	963-128	
WTB 10K-3NM	15	5	5	100	965-228	963-128	
WTB 30K-2NM	30	10	10	200	965-228	963-128	

### **BALANCES & TEST SERVICE 2024**

**KERN Pictograms** 



Conformity Assessment

conformity assessment is

specified in the pictogram

The time required for

**DAkkS** calibration

DAkkS calibration

pictogram

. The time required for

is shown in days in the

The time required for

Package shipment

The time required for

in the pictogram

Pallet shipment

in the pictogram

The time required for

internal shipping prepa-

rations is shown in days

internal shipping prepa-

rations is shown in days

in days in the pictogram

Factory calibration (ISO)

Factory calibration is shown

possible (DKD)

M

DAkkS

+3 DAYS

**ISO** 

á...



#### Internal adjusting

Quick setting up of the balance's accuracy with internal adjusting weight (motordriven)



### Adjusting program CAL

For quick setting up of the balance's accuracy. External adjusting weight required



#### **EasyTouch**

Suitable for the connection, data transmission and control through PC or tablet



#### Memory

Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.



#### Alibi memory

Secure, electronic archiving of weighing results, complying with the 2014/31/EU standard.



### KERN Universal Port (KUP)

allows the connection of external KUP interface adapters, e.g. RS-232, RS-485, SB, Bluetooth, WIFI, Analogue, Ethernet etc. for the exchange of data and control commands, without installation effort



### RS-232 Data interface

To connect the balance to a printer, PC or network



#### **RS-485 Data interface**

To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible



### USB Data interface

To connect the balance to a printer, PC or other peripherals



#### Bluetooth\* Data interface

To transfer data from the balance to a printer, PC or other peripherals



#### WIFI Data interface

To transfer data from the balance to a printer, PC or other peripherals



#### **Control outputs**

(optocoupler, digital I/O) To connect relays, signal lamps, valves, etc.



### Analogue interface

to connect a suitable peripheral device for analogue processing of the measurements



### Interface for second balance

For direct connection of a second balance



#### **Network interface**

For connecting the scale to an Ethernet network



# KERN Communication Protocol (KCP)

It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems



#### GLP/ISO log intern

The balance displays weight, date and time, independent of a printer connection



#### **GLP/ISO log Printer**

With weight, date and time. Only with KERN printers.



#### Piece counting

Reference quantities selectable. Display can be switched from piece to weight



#### Recipe level A

The weights of the recipe ingredients can be added together and the total weight of the recipe can be printed out



#### Recipe level B

Internal memory for complete recipes with name and target value of the recipe ingredients. User guidance through display



#### Totalising level A

The weights of similar items can be added together and the total can be printed out



Percentage determination Determining the deviation in % from the target value (100 %)



#### Weighing units

Can be switched to e.g. nonmetric units. See balance model. Please refer to KERN's website for more details



## Weighing with tolerance range (Checkweighing)

Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model



#### Hold function

(Animal weighing program) When the weighing conditions are unstable, a stable weight is calculated as an average value



# Protection against dust and water splashes IPxx

The type of protection is shown in the pictogram



#### Suspended weighing Load support with hook on the underside of the

balance



#### **Battery operation**

Ready for battery operation. The battery type is specified for each device



## Rechargeable battery pack

Rechargeable set



### Universal plug-in power supply

with universal input and optional input socket adapters for A) EU, CH, GB B) EU, CH, GB, US C) EU, CH, GB, US, AUS

Plug-in power supply



# 230V/50Hz in standard version for EU, CH. On request GB, USA or A

On request GB, USA or AUS version available



# Integrated power supply unit

Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, USA or AUS on request



#### Weighing principle Strain gauges

Electrical resistor on an elastic deforming body



#### Weighing principle Tuning fork

A resonating body is electromagnetically excited, causing it to oscillate



#### Weighing principle Electromagnetic force compensation

Coil inside a permanent magnet. For the most accurate weighings



#### Weighing principle Single cell technology

Advanced version of the force compensation principle with the highest level of precision



