MEASURING TECHNOLOGY & TEST SERVICE 2024

Hardness testing of metals (UCI)

Mobile Ultrasound Hardness Testing Device SAUTER HO



Premium UCI hardness testing device for Rockwell, Brinell and Vickers



Mini statistics function: Display of the measuring result, the number of measurements, the maximum and minimum value as well as the average value and the standard deviation



Scope of delivery: Standard block for calibration (approx. 61 HRC), USB cable, display unit, UCI sensor unit, transport case, software to transfer the saved data to the PC, other accessories



Test stand for repeatable movements during testing. In this way you can avoid errors which could occur in manual handling of the sensor. This ensures even more stable measurements and more precise measuring results, see *Accessories*





PREMIUM ★★★

MEASURING TECHNOLOGY & TEST SERVICE 2024

Hardness testing of metals (UCI)

Mobile Ultrasound Hardness Testing Device SAUTER HO









SAUTER

Features

- · Application: This ultrasound hardness testing device is ideally suited for mobile hardness testing, where the main emphasis is on obtaining rapid and precise results
- · Principle: The SAUTER HO measures by using a vibrating rod which vibrates at ultrasonic frequency and is pressed onto the sample at a defined test force. At the lower end there is a Vickers indenter. Its resonant frequency increases, as soon as an indentation is created when it comes into contact with the sample. Through appropriate adjustment of the device, the resulting change in resonant frequency is matched with the corresponding Vickers hardness
- · Examples: The SAUTER HO ultrasound hardness testing system is primarily used for measuring small forgings, castings, welding points, punched parts, casting tools, ball bearings and the flanks of gear wheels as well as for measuring the influence of warmth or heat
- · Advantages compared with Rockwell and Brinell: Almost non-destructive testing by smaller test force and thus only microscopic indentation craters
- Advantages compared with Vickers: Demanding optical measuring is not required. You can therefore carry out measurements directly on-site, for example, on a permanently installed workpiece
- · Advantages compared with Leeb: The high requirements concerning the proper weight of the test object can be widely omitted
- · Standards: The device meets following technical standards: DIN 50159-1; ASTM-A1038-2005; IB/T9377-2013

S

ACCU

230 V

○ ?!)

TOL

· Measurement data memory saves up to 1000 measurement groups each with 20 individual values

· Calibration: The device can be set to both standard hardness test blocks as well as to up to 20 reference calibration values. When doing this it is possible to measure different materials quickly, without having to re-adjust the device to the individual materials

Technical data

- Measuring ranges: HRC: 20,3-68; HRB: 41-100; HRA: 61-85,6; HV: 80-1599; HB: 76-618; Tensile strength: 255-2180 N/mm²
- Measurement precision: ± 3 % HV; ± 1,5 HR; ± 3 % HB
- Display units: HRC, HV, HBS, HBW, HK, HRA, HRD, HR15N, HR30N, HR45N, HS, HRF, HR15T, HR30T, HR45T. HRB.
- · Rechargeable battery pack integrated, as standard, operating time up to 12 h without backlight, charging time approx. 8 h
- · Minimum weight of the test object: 300 g for direct measurement with the sensor (included): 100 g with supporting ring (optional)
- · Minimum dimensions the test surface size around: approx, 5×5 mm (recommended)
- Overall dimensions W×D×H 28×83×160 mm
- Net weight approx. 0,95 kg

Accessories

- · External impact sensor Type D, as standard, can be reordered, SAUTER AHMO D
- 5 Calibration and adjustment plate (hardness test blocks) with defined and tested steel hardness for regular testing and adjustment of hardness testing devices. The hardness values are indicated. A key feature of the plates is the low-granular, homogenous finish of the steel, Ø 90 mm

OPTION

|SO

28 to 35 HRC, SAUTER HO-A09 38 to 43 HRC, SAUTER HO-A10 48 to 53 HRC, SAUTER HO-A11 58 to 63 HRC, SAUTER HO-A12

- 6 Test stand for repeatable movements during testing. Smooth-running mechanical system, stroke length 34 mm, maximum height of the test object within the test stand 240 mm, swivel probe device for measurements outside the base plate, very robust construction, net weight approx. 9 kg, SAUTER HO-A08
- · Motorised probe. Enables testing at the touch of a button while maintaining the same procedure (while stocks last)
- HV 0,3, SAUTER HO-A15 HV 0.5. SAUTER HO-A16 HV 0.8. SAUTER HO-A17 HV 1, SAUTER HO-A18

SAUTER HO 1K, HO 2K

- I Support ring, flat, SAUTER HO-A04N
- 2 Support ring, small cylinder, Ø 8-20 mm, SAUTER HO-A05N
- Support ring, large cylinder, Ø 20-80 mm, SAUTER HO-A06N

SAUTER HO 5K, HO 10K

- 1 Support ring, flat, SAUTER HO-A04
- 2 Support ring, small cylinder, Ø 8-20 mm, SAUTER HO-A05
- Support ring, large cylinder, Ø 20-80 mm, SAUTER HO-A06
- 4 Deep-hole protective cover, SAUTER HO-A07

Model	Hardness scale	Min. weight of test item	Min. thickness of test item	Option Factory calibration certificate
SAUTER		g	mm	KERN
HO 1K	HV 1	300	2	961-270
HO 2K	HV 2	300	2	961-270
HO 5K	HV 5	300	2	961-270
HO 10K	HV 10	300	2	961-270




STANDARD



MEASURING TECHNOLOGY & TEST SERVICE 2024

SAUTER Pictograms







Conformity assessment Models with type approval for construction of verifiable systems

SAUTER

DAkkS calibration DAkkS possible +3 DAYS

The time required for DAkkS calibration is shown in days in the pictogram

Factory calibration (ISO) ISO +4 DAYS

The time required for factory calibration is specified in the pictogram

Package shipment

1 DAY

2 DAYS

The time required for internal shipping preparations is shown in days in the pictogram

Pallet shipment

The time required for internal shipping preparations is shown in days in the pictogram

The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license Other trademarks and trade names are those of their respective owner

printers

PRINTER

or other peripheral devices

with date, time and serial

number. Only with SAUTER

CHNIEBE TRADING